



114030K21MXXXG

Cable type
14/4 AWG
black TPE

Finished Length
M005 = .5 Meters
M010 = 1 Meter

MECHANICAL
 CONTACT : GOLD/NICKEL OVER COPPER ALLOY
 INSERT : BLACK PVC
 COUPLING NUT: ZINC DIE CAST, BLACK E-COAT
 MOLDED BODY: BLACK PVC
 CABLE: 14 AWG 4 CONDUCTORS BLACK TPE JACKET
 CABLE MARKING: [MFG. UL FILE NO.] 14 AWG (2.08mm²)
 UL TYPE TC-ER/MTW (UL) THHN/THWN
 600V 90C DRY 75C WET OIL RES SUN
 RES [MFG. CSA FILE NO.] CSA AWM
 I/II A/B 105C W75 1000V -40C FT4

ELECTRICAL
 VOLTAGE RATING: 600V AC/DC
 AMPERAGE: 15A

ENVIRONMENTAL
 PROTECTION: IP67

UPDATED DRAWING EC NO: IPG2016-1628 DRWN: GGUSTAFS 2016/06/02 CHKD: MZIELINS 2016/06/15 APPR: BWOODMAN 2015/11/09	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE INCH/MM		SCALE NTS	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY	DATE	MINI CHANGE ASSEMBLY 4P MALE/FEMALE 14/4 AWG TPE BLACK MOLEX INCORPORATED				
		4 PLACES	±---	±---	KCOX01	2015/10/19					
		3 PLACES	±---	±---	CHECKED BY	DATE	TITLE MOLEX INCORPORATED DOCUMENT NO. SD-130062-023 SHEET NO. 1 OF 1				
2 PLACES	±---	±---	BARDEN	2015/10/19							
1 PLACE	±---	±---	APPROVED BY	DATE	MATERIAL NO. SEE MATRIX THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
ANGULAR ±---°			JFMURPHY	2015/11/09							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE B								