



**Product:** [5200UE](#)

Security & Sound, 2 Conductor 16 AWG, BC, CMR

## Product Description

Security & Commercial Audio Cable, Riser-CMR, 2-16 AWG stranded bare copper conductors with polypropylene insulation, PVC jacket with ripcord

## Technical Specifications

### Product Overview

Suitable Applications:	Data Circuits, Monitor/Detection, Control Circuits, Initiating Circuits, Notification Circuits
------------------------	--

### Construction Details

#### Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	2	16 AWG	19x29	BC - Bare Copper

#### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PO - Polyolefin	0.008 in (0.20 mm)	0.073 in (1.9 mm)	Black, Red

#### Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.017 in (0.43 mm)	0.180 in (4.57 mm)	Yes

Overall Cable Diameter (Nominal):	0.180 in (4.57 mm)
-----------------------------------	--------------------

### Electrical Characteristics

#### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
Conductor(s)	4.2 Ohm/1000ft	23 pF/ft (75 pF/m)	6.25 Amps per conductor @ 25°C

#### Voltage

UL Voltage Rating
300 V (CMR)

### Mechanical Characteristics

#### Temperature

UL Temperature	Operating
75°C	-20°C to +75°C

#### Bend Radius

Stationary Min.	Installation Min.
1.8 in (46 mm)	1.8 in (46 mm)

Max. Pull Tension:	59 lbs (27 kg)
Bulk Cable Weight:	24 lbs/1000ft

### Standards and Compliance

Environmental Suitability:	Indoor - Riser, Indoor
Flammability / Reaction to Fire:	UL 1666 Riser, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	Article 800, CMR
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	6200UE

## History

Update and Revision:	Revision Number: 0.509 Revision Date: 04-13-2023
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC/EAN	Footnote
5200UE 0101000	Black	Reel	1,000 ft	612825157458	
5200UE 010U1000	Black	UnReel	1,000 ft	612825421146	
5200UE 010Z1000	Black	ReelTuff Box	1,000 ft	612825157496	
5200UE 0061000	Blue, Light	Reel	1,000 ft	612825350187	
5200UE 001U1000	Brown	UnReel	1,000 ft	612825421108	
5200UE 001Z1000	Brown	ReelTuff Box	1,000 ft	612825157403	
5200UE 0011000	Brown	Reel	1,000 ft		
5200UE.00152	Chrome	Reel	152 m	8719605008008	
5200UE.00305	Chrome	Reel	305 m	8719605008015	
5200UE 008500	Gray	Reel	500 ft	612825157410	
5200UE 008U500	Gray	UnReel	500 ft	612825421122	
5200UE 0081000	Gray	Reel	1,000 ft	612825157434	C
5200UE 008U1000	Gray	UnReel	1,000 ft	612825157427	
5200UE 008Z1000	Gray	ReelTuff Box	1,000 ft	612825350194	
5200UE 0051000	Green, Dark	Reel	1,000 ft	612825350170	
5200UE 0031000	Orange	Reel	1,000 ft	612825350156	
5200UE 0021000	Red	Reel	1,000 ft	612825421115	C
5200UE 002Z1000	Red	ReelTuff Box	1,000 ft	612825350149	
5200UE 0071000	Violet	Reel	1,000 ft	612825336532	
5200UE 009U1000	White	UnReel	1,000 ft	612825421139	
5200UE 0091000	White	Reel	1,000 ft	612825157441	
5200UE 009Z1000	White	ReelTuff Box	1,000 ft	612825157465	
5200UE 0041000	Yellow	Reel	1,000 ft	612825350163	

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.