

# FireWire 800 IEEE 1394b Hi-speed Cable (9pin/6pin M/M) 6 ft. (1.83 m)

MODEL NUMBER: F017-006



### **Highlights**

- Connects Firewire 800 devices to legacy 1394a ports
- Meets FireWire 800 and 1394b Specifications
- Backward compatible to Original FireWire components

#### **Package Includes**

6-ft. (1.83 m) IEEE-1394b
FireWire 800 Gold Hi-Speed
9pin/6pin Cable

#### **Features**

- Data transfer rates to 800Mbps
- Hot Pluggable supports Plug-n-Play operation
- Premium triple-shielded cable with molded, Gold connectors
- Backward compatible with original FireWire systems and devices
- Compatible with PC, Mac, SUN, and other IEEE-1394b equipped systems

## **Specifications**

| OVERVIEW                        |                      |  |
|---------------------------------|----------------------|--|
| UPC Code                        | 037332124609         |  |
| Technology                      | FireWire             |  |
| PHYSICAL                        |                      |  |
| Color                           | Black                |  |
| Cable Jacket Color              | Black                |  |
| Cable Length (ft.)              | 6                    |  |
| Cable Length (m)                | 1.83                 |  |
| Shipping Dimensions (hwd / in.) | 8.50 x 6.90 x 0.50   |  |
| Shipping Dimensions (hwd / cm)  | 21.59 x 17.53 x 1.27 |  |
| Shipping Weight (lbs.)          | 0.17                 |  |
| Shipping Weight (kg)            | 0.08                 |  |



| CONNECTIONS                         |                           |  |
|-------------------------------------|---------------------------|--|
| Side A - Connector 1                | 9 PIN (MALE)              |  |
| Side B - Connector 1                | 6 PIN (MALE)              |  |
| STANDARDS & COMPLIANCE              |                           |  |
| Product Compliance                  | RoHS                      |  |
| WARRANTY & SUPPORT                  |                           |  |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |  |



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.