


TABLE 1	
MODEL NUMBER	LENGTH
415-0525-006	6.00±.15
415-0525-012	12.00±.25

REV	ECO	DATE
1	INITIAL RELEASE	6/24/2021



PART LIST		
ITEM	QTY	DESCRIPTION
1	1	SMPM STR FEMALE
2	1	SMPM RA FEMALE
3	AR	CABLE

NOTES: UNLESS OTHERWISE SPECIFIED.

1. CABLE ASSEMBLY DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS FOR A PERIOD OF ONE MINUTE.
2. CABLE ASSEMBLIES TO BE 100% TESTED FOR VOLTAGE AND CONTINUITY.
3. VSWR: 1.50 MAX DC-18GHz

<p>This PROPRIETARY Document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is not traced or copied without permission and is returnable upon demand.</p> <p>INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2009.</p>	Model No: 415-0525-001/999	JOHNSON		
	RoHS <input checked="" type="checkbox"/> (EU)/2015/863 COMPLIANT	Cage Code	Title: CABLE ASSY, SMPM STR FEMALE TO SMPM RA FEMALE, .086" SEMI-RIGID	
	<small>UNLESS OTHERWISE SPECIFIED UNITS: INCH</small> .XX ± .01 .XXX ± .003 .XXXX ± .0010 ANGLE ± 2°		Drawing No. 415-0525-001/999	REV. 1
	Drawn by: ROMAN YAO	Date: 6/24/2021	Size A	DO NOT SCALE DRAWING
		Workmanship Std/Sheet NONE	1 OF 1	