



SPECIFICATIONS
 Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°c to +105°c

Contact Material:Brass
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)

Dimension antitheses list			
ITEM	PA	PC	L
Standard	6.00	3.00	11.50
Alternate			

Ordering Information

XDZ 254 - * - N - Z - * - **

No. of Rows 1=Single Row 2=Dual Row	No. of Pins 02-40 Pin	Type Z=直针 W=弯针 S=芯轴 WS=带尾	Length 英寸	Contact Plating C0:Gold Flash G1:1u' Gold G2:3u' Gold G3:5u' Gold G4:10u' Gold G5:15u' Gold G6:30u' Gold S0:Gold Flash/Tin S1:tin
---	--------------------------	---------------------------------------	--------------	--

			GENERAL TOLERANCE	制图 DRAWING	深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd				
			DIM TOL	审核 CHECK		产品名称 TITLE	2.54单排 直排针-塑高2.5	版本 REV.	A
			X.X ±0.30	批准 APPROVAL		产品料号 PART NO.	XDZ254-1-N-Z-2.5-XX	单位 UNITS	mm
			X.XX ±0.20 X.XXX ±0.10	比例 SCALE		材料 MATERIAL		页次 SHEET	1/1
1	初版发行		Angle ±3.0°	投影 Projection					
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE							