



Recommended P.C.B Layout(Top Side)  
(PCB BOARD TOLERANCE±0.05)





SPECIFICATIONS

Rated Current:3.0AMP  
Contact Resistance:20mΩ Max  
Withstand Voltage:1000V AC/DC  
Insulation Resistance:1000MΩ Min  
Operation Temperature:-40°c to +105°c

Contact Material:Brass  
Contact Plating:Au Over Ni  
Insulator Material:Polyester(UL94V-0)  
Standard: PA6T  
Max.Processing Temp: 230°C for 30-60 seconds  
(260°C for 10 seconds)

Dimension antitheses list			
ITEM	PA	PC	L
Standard	6.00	3.00	11.50
Alternate			



Ordering Information

XDZ 254 - \* - N - Z - \* - \*\*

No. of Rows  
1=Single Row  
2=Dual Row

No. of Pins  
02-40 Pin

Type  
Z=直针  
W=弯针  
S=芯轴  
WS=芯轴

Length  
英寸

Contact Plating  
C0:Gold Flash  
G1:1u' Gold  
G2:3u' Gold  
G3:5u' Gold  
G4:10u' Gold  
G5:15u' Gold  
G6:30u' Gold  
S0:Gold Flash/Tin  
S1:tin

			GENERAL TOLERANCE	制图 DRAWING	深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd			
			DIM TOL	审核 CHECK	产品名称 TITLE	2.54 双排 直排针 塑高2.5	版本 REV.	A
			X.X ±0.30	批准 APPROVAL	产品料号 PART NO.	XDZ254-2-N-Z-2.5-XX	单位 UNITS	mm
			X.XX ±0.20	比例 SCALE	材料 MATERIAL		页次 SHEET	1/1
			X.XXX ±0.10	投影 Projection				
			Angle ±3.0°					
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						