
TRIPP-LITE

Power Extension Cord, Right-Angle NEMA 5-15P to NEMA 5-15R - Heavy-Duty, 15A, 120V, 14 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: P024-006-15D







6 ft. extension cord with 5-15R and right-angle 5-15P connectors connects your server to a PDU, UPS, surge protector or wall outlet.

Features

Heavy-Duty Extension Cable for Network Devices That Require a Heavy-Gauge ConnectionThis 6ft. (1.83 m) extension cord features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. It can be used to connect a computer, server or other device with a NEMA 5-15P plug to a PDU, UPS system, surge protector or wall outlet with a NEMA 5-15R outlet. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

Right-Angle Plug Makes Connecting in Tight Spaces EasierThe space-saving right-angle NEMA 5-15P connector is easy to install in confined spaces, such as behind your computer desk or workstation. The right-angle construction also relieves strain on the cable and connector and prevents the cable from bending awkwardly.

Specifications

OVERVIEW		
UPC Code	037332243874	
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU	
Country/Region	North America	
INPUT		
Maximum Input Amps	15	
Voltage Compatibility (VAC)	125	

Highlights

- Recommended for powering computers, servers and other home/office peripherals
- Right-angle plug allows easier connection in confined or hardto-reach spaces
- Heavy-duty cord replaces or upgrades standard power cord provided by manufacturer
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for worn-out or missing 6-ft. (1.83 m) extension cord

Applications

- Connect devices like computers, servers and monitors to a PDU in your data center
- Extend an existing power connection up to 6-ft. (1.83 m) to more easily place a device or reach a power source in a rack
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

 P024-006-15D Heavy-Duty 6-ft. (1.83 m) Extension Cord, Right-Angle NEMA 5-15P to NEMA 5-15R, Black

TRIPP-LITE

PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	9.3mm
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm²)	2.08
Cable Length (ft.)	6
Cable Length (m)	1.83
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	10% to 65% RH
Storage Humidity Range	10% to 65% RH
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P - RIGHT ANGLE
Side B - Connector 1	NEMA 5-15R
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	Yes
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



1000 Eaton Boulevard Cleveland, OH 44122 United States



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.