

# Power Extension Cord, C19 to C20 - Heavy-Duty, 20A, 250V, 12 AWG, 2 ft. (0.61 m), Black

MODEL NUMBER: P036-002









C19 to C20 20A heavy-duty extension cable connects high-output devices with C19/C20 power connectors, including blade server chassis.

#### **Features**

**20A C20-to-C19 Power Cable for Network Devices That Require a Heavy-Gauge Connection**This heavy-duty extension cord features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This cord can be used to connect a server, router, network switch or blade server enclosure to a UPS system or PDU or replace or upgrade the standard power cord provided by the device's manufacturer. The 2-ft. (0.61 m) length helps reduce cable clutter and minimize the risk of tripping.

#### **Highlights**

- Recommended for powering servers, routers and other highoutput network devices
- 2-ft. (0.61 m) length allows flexibility in placing devices, while avoiding cable clutter
- C20 to C19 cord replaces or upgrades standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment

### **Applications**

- Connect devices like computers, servers and monitors to a PDU up to 2-ft. (0.61 m) away in your data center
- Extend an existing power connection up to 2-ft. (0.61 m) to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

#### **Package Includes**

 P036-002 C19 to C20 Heavy-Duty Extension Cord, 2-ft. (0.61 m), Black

## **Specifications**

OVERVIEW		
UPC Code	037332141613	
Device Compatibility	Server; Router; Network Switch; UPS; PDU	
Country/Region	North America	
INPUT		
Maximum Input Amps	20	
Voltage Compatibility (VAC)	100-250	
PHYSICAL		
Plug Color	Black	
Cable Jacket Color	Black	
Cable Jacket Material	PVC	



Cable Jacket Rating	VW-1	
Power Cord Jacket Type	SJT	
Cable Outer Diameter (OD)	11mm	
Number of Conductors	3	
Wire Gauge (AWG)	12	
Wire Gauge (OD - mm²)	3.31	
Cable Length (ft.)	2	
Cable Length (m)	0.61	
Shipping Dimensions (hwd / in.)	12.80 x 8.90 x 0.50	
Shipping Dimensions (hwd / cm)	32.51 x 22.61 x 1.27	
Shipping Weight (lbs.)	0.55	
Shipping Weight (kg)	0.25	
ENVIRONMENTAL		
Operating Temperature Range	-4° to 140°F (-20° to 60°C)	
Storage Temperature Range	-4° to 140°F (-20° to 60°C)	
Operating Humidity Range	10% to 65% RH	
Storage Humidity Range	10% to 65% RH	
CONNECTIONS		
Side A - Connector 1	IEC-320-C20	
Side B - Connector 1	IEC-320-C19	
FEATURES & SPECIFICATIONS		
Antibacterial	No	
Angled Plug	No	
High Voltage	Yes	
Locking Plug	No	
Coiled Power Cord	No	
STANDARDS & COMPLIANCE		
Product Certifications	cUL Listed; UL Listed	
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	







© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.