



Plug Component			Plug Strip Dimension			Wire Spec.	Terminal ROJ & Strip			Terminal Component		
Color	Component	Qty	Strip	ROJ	Color	SJT 14AWGX3C 105°C BLACK Length: 1500±50 mm	Strip	ROJ	Color	Component	Color	Qty
40P Black 90±5°A	LT-602(15A 250V) (IEC 320 C14)	1	5±1	20±3	Black		7±1	20±3	Black	IEC 320 C13 (LT-501(15A 250V))	40P BK 90±5°A	1
BLACK	(602 Inner Body)	1	5±1	20±3	White		7±1	20±3	White	computer power cord terminals	Copper	3
Nickel-Plated	2*4(Solid Blades)	3	5±1	23±3	Green		7±1	20±3	Green	(501 Inner Body)	White	1

Marking:

RHYTHM: (UL) E88231 SJT 3X14AWG(2.08mm²)
105°C 300V VW-1 CSA LL54496 SJT
3X14AWG(2.08mm²)105°C 300V VW-1
RHYTHM R

NOTE :

1. PLUG : LT-602 AMERICAN TYPE
2. CONNECTOR : LT-501 IEC-320 C13
3. CORD : SJT 14AWGX3C 105°C BLACK 1.5M
4. APPROVALS : UL, C-UL
5. Supplier for flexible cord : RHYTHM
6. Hi-Pot Test:2000v/1min<1mA>

Modification History

		DRAWER	Eric	DATE	20/10/24	P/N	800-1400-2-SJT0-BL-00150-1
		APPROVE		REV.	0	Dr.No.	1091098
			比例	TOL.	±5mm		
DESCRIPTION	DATE			ALL DIMENSIONS IN mm			

CnC Tech
Industrial Cable and Connector Technology