

Specification Sheet

Part Number: 157-00060



Wide strap minimizes pinching of soft hoses and convoluted tubing.
Clamping rails increase circumferential grip on varying bundle diameters.
Locking stud mount pawls allow for easy hand insertion.
Nut or weld nesting counterbore provides flush mounting at the base.

Stand Off Dual Clamp Tie, 26.10" Long, 0.31" Stud Dia, PA66HIRHSUV, Black, 250/pkg

Article Number 157-00060

Type SDCTL

Color Black (BK)

Quantity Per bag

Product Description Stand Off Dual Clamp Ties offer the same features as the standard dual clamp tie, with a standoff mount that secures the bundle away from the side of the frame rail. This protects the bundles from bolts and other protrusions.

Short Description Stand Off Dual Clamp Tie, 26.10" Long, 0.31" Stud Dia, PA66HIRHSUV, Black, 250/pkg

Global Part Name SDCTL-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)	100.0
Minimum Tensile Strength (Metric)	445.0
Length L (Imperial)	26.1
Length L (Metric)	663.0
Fixation Method	Weld Stud Fixing
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.5
Width W (Metric)	12.7
Bundle Diameter Min (Imperial)	0.375
Bundle Diameter Min (Metric)	9.5
Bundle Diameter Max (Imperial)	3.4
Bundle Diameter Max (Metric)	86.4
Height H (Imperial)	1.47
Height H (Metric)	37.30

Stud Diameter (Metric)	M8
Stud Diameter (Imperial)	5/16
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	250
Package Quantity (Metric)	250
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar,

electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)