

Computer Cable, 15-ft. Bi-Directional Parallel Printer Cen36M to DB25M

MODEL NUMBER: P602-015



Highlights

- Superior molded cables with integral strain relief and foil-shielding for maximum EMI/RFI protection
- Provides superior conductivity and support for high-speed bi-directional printing

System Requirements

- Computers with a DB25 Female parallel port
- Parallel printers with a Centronics 36 Female parallel port with Bi-Directional communication (although not essential).

Package Includes

- 15-ft. Bidir Parallel Cable Cen36M to DB25M

Description

Tripp Lite's 15-ft. bi-directional parallel printer cable connects computers with a DB25 female parallel port to parallel printers with a Centronics 36 female parallel port. The cable has DB25 male/Cent36 male connectors and supports bi-directional communication. It is manufactured from superior molded cable with integral strain relief and foil shielding for maximum EMI/RFI protection. Bi-directional communication allows your printer to broadcast printer error messages back to network computers. Use IEEE cable if IEEE specifications are required. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Features

- Supports bi-directional communication
- Length 15-ft. Connectors: DB25 male/Cent36 male
- Superior molded cable with integral strain relief and foil shielding for maximum EMI/RFI protection
- Bi-directional communication allows your printer to broadcast printer error messages back to network computers
- Molded ends with easy-grip textured overmold
- Use IEEE cable if IEEE specifications are required

Specifications

OVERVIEW	
UPC Code	037332013453
PHYSICAL	
Cable Length (ft.)	15
Cable Length (m)	4.57

Shipping Dimensions (hwd / in.)	12.50 x 10.00 x 1.00
Shipping Dimensions (hwd / cm)	31.75 x 25.40 x 2.54
Shipping Weight (lbs.)	0.94
Shipping Weight (kg)	0.43
CONNECTIONS	
Side A - Connector 1	DB25 (MALE)
Side B - Connector 1	CENTRONICS 36 (MALE)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty