


**SEE PAGE 2 FOR DETAILS



4 = WHITE

INCHES

O1 = WIRING SCHEMATIC 1

O2 = WIRING SCHEMATIC 2

LENGTH

EX: 06 = 6 INCHES

12 = 12 INCHES

NOTE: PACKAGED 10 PER BAG

4 = BLACK

RoHS COMPLIANT

风

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
G. BROWN

DATE:
01/23/2019


UNITS IN INCHES [MM] DO NOT SCALE FROM DRAWING





 SCALE:
 SHEET
 OF
 REV

 NTS
 1
 2
 3

FPM12A04IYYAR0Y









NOTE: MATERIAL HDUSING: PBT UL94V-0, BLACK CONTACT: **BRASS** NUT: **BRASS** SHELL: **BRASS** D-RING: EPDM, BLACK **FINISH** CONTACT: GOLD PLATED, 10 µ" Min. UNDER PLATE: NICKEL NICKEL PLATED NUT: SHELL: NICKEL PLATED **ELECTRICAL** RATED CURRENT: 4A RATED VOLTAGE: 250V INSULATION RESISTANCE: 100ΜΩ ΜΙΝ CONTACT RESISTANCE: $10m\Omega$ MAX WATER PROOF: IP67/68 **ENVIRONMENT**

OPERATION TEMPERATURE: -40°C ~ +85°C

RECOMMENDED PANEL CUT-OUT





ROHS COMPLIANT

例

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
G. BROWN

DATE:
01/23/2019

UNITS IN INCHES [MM] DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS DWG NO.	SHEET	2	OF	2	REV 3
JWG NO.	FPM12A04IYYAR0Y				