

Duplex Multimode 62.5/125 Fiber Patch Cable (LC/LC) - Red, 20M (65 ft.)

MODEL NUMBER: N320-20M-RD



Highlights

- Manufactured from 62.5/125 duplex (Zipcord) fiber with Red jacket
- Length: 20 meter Connectors: LC connector on each end
- Insertion loss testing performed on every connector (0.2dB typical

System Requirements

 Any fiber optic hardware or NIC card requiring multimode duplex cable with LC connectors

Package Includes

 20M Duplex MMF Cable LC/LC 62.5/125 Micron Fiber Red Jacket

Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- Red PVC jacket
- Length: 20 meter Connectors: LC connector on each end
- Fiber made from glass (not a polymer)
- Fiber optic distributed data interface (FDDI)and OFNR rated

Specifications

OVERVIEW	
UPC Code	037332130815
Technology	Multimode
Optical Mode	OM1
PHYSICAL	
Cable Jacket Color	Red
Connector Color	Gray
Cable Jacket Material	LSZH
Cable Jacket Rating	OFNR
Clad Diameter (microns)	125
Core Diameter (microns)	62.5
Number of Fibers	2



Cable Length (ft.)	65.6	
Cable Length (m)	20.00	
Cable Length (in.)	787.4	
Minimum Bend Radius	20MM (Dynamic); 10MM (Static)	
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.80	
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 2.03	
Shipping Weight (lbs.)	0.25	
Shipping Weight (kg)	0.11	
ENVIRONMENTAL		
Operating Temperature Range	-4 to 140 °F (-20 to 60 °C)	
Storage Temperature Range	-4 to 140 °F (-20 to 60 °C)	
Operating Humidity Range	5% to 85% RH, Non-Condensing	
Storage Humidity Range	35% to 65% RH, Non-Condensing	
COMMUNICATIONS		
Network Compatibility	1 Gbps (Gigabit); 10 Gbps	
Attenuation @ 850NM	3.0dB/Km	
Insertion Loss	0.20dB	
CONNECTIONS		
Side A - Connector 1	LC DUPLEX (MALE)	
Side B - Connector 1	LC DUPLEX (MALE)	
Endface Polish	PC	
FEATURES & SPECIFICATIONS		
Push/Pull Tabs	No	
Breakout	No	
Trunk	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; REACH	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	
Product Warranty Period	Lifetime limited warranty	







© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.