

Easy Pull Long-Run Display Cable - Type-B Digital PVC Trunk Cable, 25 ft. (7.62 m)

MODEL NUMBER: EZB-025



Highlights

- Versatile trunk cable allows for a variety of connection options
- Easily pulls through conduit or confined spaces with included end caps with integrated pull tabs
- UL20276 Digital Video Cable supports 1080p
- Requires a signal booster, such as Tripp Lite's B120-000 (DVI) or B122-000-60 (HDMI)

Package Includes

- Easy Pull Type-B Digital PVC Trunk Cable, 25 ft.

Features

- Eliminates the need to field terminate HDMI and DVI connectors
- Detachable, screw-on connectors
- Allows cable to be run according to code - inside conduit, drop ceilings, etc.
- Makes pulling long cables fast and easy
- Protects entire cable from strain, dirt, debris and damage
- Choose from a variety of connector combinations for the perfect fit
- Also available in 25t. and 100 ft. PVC lengths (Plenum cables available upon request)
- UL20276 Digital Video Cable supports 1080p
- Requires a signal booster, such as Tripp Lite's B120-000 (DVI) or B122-000-60 (HDMI)

Specifications

OVERVIEW	
UPC Code	037332146861
Technology	DVI; HDMI
Cable Type	Passive
PHYSICAL	
Color	Black; Yellow
Cable Jacket Color	Black; Yellow
Cable Length (ft.)	25
Cable Length (m)	7.62

TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard
Cleveland, OH 44122
United States

Shipping Dimensions (hwd / in.)	1.00 x 7.50 x 10.00
Shipping Dimensions (hwd / cm)	2.54 x 19.05 x 25.40
Shipping Weight (lbs.)	1.00
Shipping Weight (kg)	0.45
CONNECTIONS	
Side A - Connector 1	DIN 19 PIN (FEMALE)
Side B - Connector 1	DIN 19 PIN (FEMALE)
Latching or Gripping Connector	No
FEATURES & SPECIFICATIONS	
IP68 Rated	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.