

USB cable type B, female USB A, IP67, male USB A, IP20, with M20 screw sealing, further information, Quantity and content: See technical data



Figure similar

General information	
Product type designation	Connecting cable USB
Control elements	
Connection type	
<ul style="list-style-type: none"> USB 	Yes; USB 2.0 Typ x IP67 to Typ A IP20
Degree and class of protection	
IP (all-round)	On the female side up to IP65 screw connection, then IP20
Standards, approvals, certificates	
CE mark	No; No CE marking obligation
RoHS conformity	Yes
Ambient conditions	
Suited for indoor use	Yes; Always comply with the operating instructions of the target device.
Ambient temperature during operation	
<ul style="list-style-type: none"> min. max. 	0 °C 55 °C
Ambient temperature during storage/transportation	
<ul style="list-style-type: none"> min. max. 	-20 °C 60 °C
Relative humidity	
<ul style="list-style-type: none"> Operation, max. 	95 %
Cables	
Cable length	2.5 m
smallest bending radius	0 mm; 10x d (cable diameter)
Color of cable sheath	Black
Mechanics/material	
Enclosure material (front)	
<ul style="list-style-type: none"> Plastic 	Yes; Connector enclosure
Torques/forces	
<ul style="list-style-type: none"> Tightening torque, min. Tightening torque, max. 	1 N·m; Hand-tight 1.5 N·m; Hand-tight
Scope of supply	
Delivery quantity in pieces	1; USB 2.0 cable (max. 500 mA)
Other	
Merchandise	Yes; USB-IP67-2500M-C7294-Siemens
Manufacturer name	GETT Gerätetechnik GmbH
Manufacturer's address	Mittlerer Ring 1, 08233 Treuen (Vogtland), Germany
Target devices	For Panels and PC systems with suitable interface; observe operating instructions of the target device!
Note:	Request certificates and drawings from manufacturer

Usable in the following products

• Product 1	6AV6881-0AU14-*
• Product 2	6AV6881-0AU14-0DB0
• Product 3	6AV6881-0AU14-1DB0
• Product 4	6AV2124-*
• Product 5	6AV2125-*
• Product 6	6AV2145-*
• Product 7	6AV7250-*
• Product 8	6AV7251-*
• Product 9	6AV7863-7*
• Product 10	6AV2128-3*
• Product 11	6AV6881-0AU14-0DB0
• Product 12	6AV6881-0AU14-1DB0
• Product 13	6AV6642-0BD01-3AX0
• Product 14	6AV6642-0BC01-1AX1
• Product 15	6AV6642-0DC01-1AX0
• Product 16	6AV6642-0DA01-1AX0
• Product 17	6AV6642-0EA01-3AX0
• Product 18	6AV6545-0CC10-0AX0
• Product 19	6AV6545-0AH10-0AX*
• Product 20	6AV6545-0DA10-0AX0
• Product 21	6AV6545-0DB10-0AX0
• Product 22	6AV6644-*
• Product 23	6AV6643-*
• Product 24	6AV2123-2*
• Product 25	6AV7862-2BC*
• Product 26	6AV7862-2BD*
• Product 27	6AV7862-2BE*
• Product 28	6AV7862-2BF*

last modified:

4/21/2021 