


| ITEM | PART# | DESCRIPTION | QTY | UOM |
|------|-----------|---|-----|-----|
| A,B | 510650500 | Micro-Latch 2.0 Rec Housing 5P | 2 | PC |
| C | 503728000 | Micro-Latch 2.0 Crimp R Term Tin #22-26 | 10 | PC |
| D | -- | PAPER PRINTED PAPER WHITE (S100X150YAJ) | 1 | PC |

| FROM | TO | DESCRIPTION | COLOR |
|------|----|--------------------------------|-------|
| A1 | B5 | 1X22AWG DISC SR-PVC BK UL10002 | BLACK |
| A2 | B4 | 1X22AWG DISC SR-PVC BK UL10002 | BLACK |
| A3 | B3 | 1X22AWG DISC SR-PVC BK UL10002 | BLACK |
| A4 | B2 | 1X22AWG DISC SR-PVC BK UL10002 | BLACK |
| A5 | B1 | 1X22AWG DISC SR-PVC BK UL10002 | BLACK |



| TABLE | | | |
|-------------|-------|----------|--|
| PART NUMBER | L1 | L2 (REF) | TITLE |
| 2196781050 | 50±3 | 15 | Micro Latch 2.0 R-R 5ckt 50mm disc Sn |
| 2196781051 | 100±3 | 15 | Micro Latch 2.0 R-R 5ckt 100mm disc Sn |
| 2196781052 | 150±4 | 15 | Micro Latch 2.0 R-R 5ckt 150mm disc Sn |
| 2196781053 | 300±4 | 15 | Micro Latch 2.0 R-R 5ckt 300mm disc Sn |
| 2196781054 | 600±6 | 15 | Micro Latch 2.0 R-R 5ckt 600mm disc Sn |

NOTES

1. Cable assembly must pass 100% continuity and polarity test.
2. Connector view shown is from mating side.
3. Label text must be 2mm max. in height with Arial font.
4. Label must be wrapped in Flag type on a single cable.

MOLEX P/N
MOLEX
BATCH WK/YR
DETAIL A

| REVISION | | | |
|------------|-----|-----------------|---------|
| DATE | REV | DESCRIPTION | CHANGER |
| 2022/02/27 | A | INITIAL RELEASE | SAIKIG |

| | | | | | |
|---|---|-----------------------------|------------------------------|--------------------------|--------------|
| FUNCTIONAL SYMBOLS $\frac{F}{A} = 0$ $\frac{F}{E} = 0$ $\frac{F}{P} = 0$ DIVISIONAL SYMBOLS | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION | | CURRENT REV DESC: | | |
| | DIMENSION UNITS | SCALE | EC NO: 697300 | | |
| | mm | NTS | DRWN: SAIKIG 2022/02/21 | | |
| | GENERAL TOLERANCES (UNLESS SPECIFIED) | | CHK'D: MNARAYAN01 2022/03/08 | | |
| ANGULAR TOL ± ° | | APPR: MNARAYAN01 2022/03/08 | | PRODUCT CUSTOMER DRAWING | |
| 4 PLACES ± | | INITIAL REVISION: | | DOCUMENT NUMBER | DOC TYPE |
| 3 PLACES ± | | DRWN: SAIKIG 2022/02/21 | | 2196781050 | PSD |
| 2 PLACES ± | | APPR: MNARAYAN01 2022/03/08 | | 000 | REVISION |
| 1 PLACE ± | | MATERIAL NUMBER | | GENERAL MARKET | A |
| 0 PLACES ± | | SERIES | | SEE TABLE | SHEET NUMBER |
| DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS | | THIRD ANGLE PROJECTION | DRAWING | A4-SIZE | 219678 |