



Product: [5002UP](#)

Audio Cable, 4 Conductor 12 AWG, BC, CL3

Product Description

Audio Cable, 4 Conductor 12 AWG, highly flexible stranded (65x30) bare copper conductors with PVC insulation, CL3, PVC jacket with ripcord

Technical Specifications

Product Overview

Suitable Applications:	High Flex Audio/Speaker
------------------------	-------------------------

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	4	12 AWG	65x30	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.023 in (0.58 mm)	0.138 in (3.51 mm)	Black, White, Red, Green

Outer Shield

Material
No Shield

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.022 in (0.56 mm)	0.377 in (9.58 mm)	Yes

Overall Cable Diameter (Nominal):	0.377 in (9.58 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
Conductor(s)	1.56 Ohm/1000ft	32 pF/ft (100 pF/m)	24 Amps per conductor @ 30°C

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	-20°C to +75°C

Bend Radius

Stationary Min.	Installation Min.
3.7 in (94 mm)	3.7 in (94 mm)

Max. Pull Tension:	338 lbs (153 kg)
--------------------	------------------

Bulk Cable Weight:	113 lbs/1000ft
--------------------	----------------

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum)
Flammability / Reaction to Fire:	UL 1685 UL loading
NEC / UL Compliance:	Article 725, CL3
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.508 Revision Date: 04-13-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
5002UP 010500	Black	Reel	500 ft	612825155720
5002UP 0101000	Black	Reel	1,000 ft	612825155799
5002UP D15500	Blue	Reel	500 ft	611589226523
5002UP 008500	Gray	Reel	500 ft	612825155768
5002UP 0081000	Gray	Reel	1,000 ft	612825155751
5002UP 005500	Green, Dark	Reel	500 ft	612825155744
5002UP 009500	White	Reel	500 ft	612825155782
5002UP 0091000	White	Reel	1,000 ft	612825155775

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.