

## Specification Sheet

Part Number: 156-01807

Delivers high extraction force for reliable performance, yet it's easy to install.

Reusable fastener can be removed from threaded or nonthreaded holes using a 5/16" hex driver.

Heat stabilized material provides excellent resistance to high temperatures.



Blind Hole Mount Outside Serrated Tie, 1/4" Thread/Non-Thread Hole, 6"L, 50lb, PA66HS, Black, 500/bag

Article Number 156-01807

Type T50SOSBHMB

Color Black (BK)

Quantity Per bag

Product Description HellermannTyton Blind Hole Mount Cable Ties for threaded and nonthreaded holes offer an easy-to-use method for bundling and affixing cables. The 2-piece design includes a heat stabilized cable tie and formula-matched, 1/4" mount that features a low insertion force and aggressively resists pull off. Performs equally well in threaded or nonthreaded blind holes. Mount can slide along cable tie to adjust orientation if needed. Fastener can be removed from hole using a hex driver. This ensures fastener can be reused.

Short Description	Blind Hole Mount Outside Serrated Tie, 1/4" Thread/Non-Thread Hole, 6"L, 50lb, PA66HS, Black, 500/bag
Global Part Name	T50SOSBHMB-PA66HS-BK
Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225.0
Length L (Imperial)	6.0
Length L (Metric)	150.0
Identification Plate Position	none
Width W (Imperial)	0.31
Width W (Metric)	7.8
Bundle Diameter Min (Imperial)	0.10
Bundle Diameter Min (Metric)	2.5
Bundle Diameter Max (Imperial)	1.40
Bundle Diameter Max (Metric)	35.0
Height H (Imperial)	0.736
Height H (Metric)	18.7
Diameter D (Imperial)	0.25

Diameter D (Metric)	6.35
Mounting Hole Diameter D (Imperial)	0.25
Mounting Hole Diameter D (Metric)	6.35 mm
Mounting Hole Diameter D Min (Imperial)	0.246
Mounting Hole Diameter D Max (Imperial)	0.254
Mounting Hole Diameter D Max (Metric)	6.45
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500

Package Quantity (Metric) 500

Customs Number 3926909988

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)