

Hi-Speed USB to IEEE 1284 Parallel Printer Gold Adapter Cable (USB-A to DB25 M/F), 6 ft. (1.83 m)

MODEL NUMBER: U207-006







Highlights

- Converts USB to IEEE-1284 Parallel DB25 Female
- Bus Powered No external power required
- Plug-n-Play Installation

System Requirements

- USB 1.1 or 2.0 port
- Windows 2000 / XP/ Vista / WIN7 / WIN8 / WIN10 OS

Package Includes

- U207-006 USB to Parallel Printer Adapter Cable - 6-ft. (1.83 m)
- User Manual

Features

- Converts USB to IEEE-1284 Parallel DB25 Female
- Bus Powered No external power required
- Plug-n-Play Installation for Windows 2000 / XP / Vista / WIN7 / WIN8 / WIN10
- USB 1.1 Compliant
- Bus Powered No External Power Supply needed

Specifications

OVERVIEW		
UPC Code	037332155764	
Technology	Parallel	
PHYSICAL		
Color	Black	
Color	DidUK	
Cable Jacket Color	Black	
Cable Length (ft.)	6	
Cable Length (m)	1.83	
Shipping Dimensions (hwd / in.)	6.70 x 4.70 x 0.10	
Shipping Dimensions (hwd / cm)	17.02 x 11.94 x 0.25	
Shipping Weight (lbs.)	0.30	
Shipping Weight (kg)	0.14	



Tripp Lite1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234

CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	DB25 (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies