

Specification Sheet

Part Number: 166-90204

Flame retardant material; meets low flammability, smoke and toxicity

ratings.

Easy to use and cut; reduces installation time and labor costs.

Flexible, abrasion resistant and durable for a variety of applications.

Good impact strength; recovers quickly if crushed.

Rated UL94 V0.

UV resistant; suitable for use in outdoor applications.

Offered in fine or course corrugated pitch.



HelaGuard Non-Metallic Conduit, Flame Retardant, Std Wt, 0.75" Dia, PA6-FR, Bk, 100 ft/Std. Reel

Article Number 166-90204

Type HG-FR0750

Color Black (BK)

Quantity Per reel

Product Description A standard weight corrugated conduit made of a flame retardant

material for use in applications in which high fire protection and low flammability are primary requirements. Easy to cut and use, the material is highly resistant to solvents and oils. Combine with

HelaGuard Non-Metallic Fittings for IP66 rating or greater protection

against water, wind and dirt.

Short Description	HelaGuard Non-Metallic Conduit, Flame Retardant, Std Wt, 0.75" Dia, PA6-FR, Bk, 100 ft/Std. Reel
Global Part Name	HG-FR0750-PA6FR-BK
Length L (Imperial)	100.0
Length L (Metric)	30.5
Inner Diameter D (Imperial)	0.86
Inner Diameter D (Metric)	21.7
Outside Diameter OD (Imperial)	1.13
Outside Diameter OD (Metric)	28.5
Nominal Diameter (Imperial)	0.75
Nominal Diameter (Metric)	28
Material	Polyamide 6, flame retardant (PA6FR)
Material Shortcut	PA6FR
Flammability	UL 94 V-0

Yes

Halogen Free

UV Resistant (Yes/No)

No

Operating Temperature

-40°F to +248°F (-40°C to +120°C)

Reach Compliant (Article 33)

Yes

ROHS Compliant

Yes

Certification/Specification

ASTM E 162 ASTM E 662 Exova | NFPA130: 2017 ASTM 1354

UL Recognized (US)

Yes

Yes

UL Recognized (US and Canada)

Package Quantity (Imperial) 100

Package Quantity (Metric) 30.48

Customs Number 3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.