

## Specification Sheet

Part Number: T120MR0H4

Screw-mount style delivers low insertion and high extraction force. Fasten with a screw or bolt to provide secure routing of cable bundles.

Choose from several tensile strengths and lengths to accommodate a range of applications.



1-Pc Cable Tie/Screw Mount, 15.6" L, 0.25" Hole, 4.02" Max Bundle Dia, 120lb, PA66, Black, 500/pkg

Article Number 113-00011

Type T120MR

Color Black (BK)

Quantity Per bag

Product Description One-piece Screw Mount Cable Ties fasten with a screw or bolt to provide secure routing of cable bundles. Multiple configurations are available to cover a range of bundle sizes and tensile strengths.

Short Description 1-Pc Cable Tie/Screw Mount, 15.6" L, 0.25" Hole, 4.02" Max Bundle Dia, 120lb, PA66, Black, 500/pkg

Global Part Name T120MR-PA66-BK

Minimum Tensile Strength (Imperial)	120
Minimum Tensile Strength (Metric)	535
Length L (Imperial)	15.6
Length L (Metric)	395.0
Fixation Method	Screw Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.30
Width W (Metric)	7.6
Bundle Diameter Min (Imperial)	0.20
Bundle Diameter Min (Metric)	5.0
Bundle Diameter Max (Imperial)	4.02
Bundle Diameter Max (Metric)	102.0
Thickness T (Imperial)	0.07

Thickness T (Metric)	1.8
Cable Tie Head Length (Imperial)	1.1
Cable Tie Head Width (Imperial)	0.5
Height H (Imperial)	0.31
Height H (Metric)	7.9
Mounting Hole Diameter D (Imperial)	0.26
Mounting Hole Diameter D (Metric)	6.5 mm
Mounting Hole Diameter D Min (Imperial)	0.26
Mounting Hole Diameter D Max (Imperial)	0.26
Mounting Hole Diameter D Max (Metric)	6.5
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)

Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL 62275
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)