TRIPP·LITE by **FATON**

Extension Cord Y Splitter, NEMA 5-15P to 2x NEMA 5-15R - 10A, 120V, 18 AWG, 1 ft. (0.31 m), Black

MODEL NUMBER: P022-001-2



Extension cord splitter allows two devices with NEMA 5-15P plugs to share one AC power input cord and one NEMA 5-15R outlet.

Features

Y-Style Power Cord Splitter Connects 2 Devices with 5-15P Plugs to One AC Outlet This extension cable splitter allows two devices with NEMA 5-15P plugs to share one AC input cord and one NEMA 5-15R outlet. The AC power splitter features a 5-15P plug for connecting to an AC power source and two 5-15R ends for connecting to devices' power cords. By connecting two devices to one outlet, the 1-ft. (0.3 m) splitter frees up space in a PDU or surge protector and allows welcome flexibility in placing equipment with respect to the power outlet.

Dual Cable Powers a Wide Variety of Essential ElectronicsWith this extension cord splitter, a single NEMA 5-15R outlet can power two devices, such as computers, monitors, printers, instrument amplifiers and other equipment compatible with a NEMA 5-15P plug. Ideal for areas where AC outlets are limited, such as rack cabinets, this extension cord Y splitter is compatible with power and extension cords.

125

Specifications

Voltage Compatibility (VAC)

OVERVIEW	
UPC Code	037332138101
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	10

Highlights

- · Connects 2 devices to one AC outlet to save space and reduce cable clutter
- Recommended for powering dual computers, monitors or other compatible peripherals
- Adds 1-ft. (0.31 m) to your existing power connection to provide flexibility in placing devices
- Ideal replacement for a worn-out or missing extension cord Y splitter
- NEMA 5-15P plug connects to AC power; 5-15R ends connect to devices' cords

Applications

- Connect 2 devices like computers, monitors, scanners and printers to one power outlet up to 1-ft. (0.31 m) away in your home office, work space or dorm room
- · Cut cable clutter by powering both monitors in a dual-monitor display mount with a single cord
- Save space in a 0U vertical rack-mount PDU by plugging two rack devices into one outlet

Package Includes

 P022-001-2 Extension Cord Y Splitter, 1-ft. (0.31 m), Black

TRIPP-LITE

1000 Eaton Boulevard Cleveland, OH 44122 United States

PHYSICAL		
Plug Color	Black	
Cable Jacket Color	Black	
Cable Jacket Material	PVC	
Cable Jacket Rating	VW-1	
Power Cord Jacket Type	SJT	
Cable Outer Diameter (OD)	7.8mm	
Number of Conductors	3	
Wire Gauge (AWG)	18	
Wire Gauge (OD - mm ²)	0.82	
Cable Length (ft.)	1	
Cable Length (m)	0.30	
Shipping Dimensions (hwd / in.)	10.00 x 7.00 x 0.50	
Shipping Dimensions (hwd / cm)	25.40 x 17.78 x 1.27	
Shipping Weight (lbs.)	0.40	
Shipping Weight (kg)	0.18	
ENVIRONMENTAL		
Operating Temperature Range	-4° to 140°F (-20° to 60°C)	
Storage Temperature Range	-4° to 140°F (-20° to 60°C)	
Operating Humidity Range	10% to 65% RH	
Storage Humidity Range	10% to 65% RH	
CONNECTIONS		
Side A - Connector 1	NEMA 5-15P	
Side B - Connector 1	(2) NEMA 5-15R	
FEATURES & SPECIFICATIONS		
Antibacterial	No	
Angled Plug	No	
High Voltage	No	
Locking Plug	No	
Coiled Power Cord	No	
STANDARDS & COMPLIANCE		
Product Certifications	cUL Listed; UL Listed	



1000 Eaton Boulevard Cleveland, OH 44122 United States

Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.