

6

5

4

3

2


1

APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/13/15	
A		ADDED 1FT PART NUMBER	5/3/19	AY/TW

CUSTOM CABLE ASSEMBLIES ARE NON-CANCELLABLE/NON-RETURNABLE



PIN ASSIGNMENT			
P1			P2
1	— RED —		1
2	— WHITE —	XXXXXX	2
3	— GREEN —		3
4	— BLACK —		4
SHELL	— BRAID —		SHELL

ADAM P/N	L
CA-USB-AM/AF-1FT	12.008" ± .787" [305 ± 20mm]
CA-USB-AM/AF-3FT	36.024" ± 1.181" [915 ± 30mm]
CA-USB-AM/AF-6FT	72.047" ± 1.969" [1830 ± 50mm]
CA-USB-AM/AF-10FT	120.079" ± 1.969" [3050 ± 50mm]

**SPECIFICATIONS:**

**Connector:**

P1= USB Connector 2.0 A Type Plug, Insulator Color: White, Overmold Color: Black, 50P PVC

P2= USB Connector 2.0 A Type Socket, Insulator Color: White, Overmold Color: Black, 50P PVC

**Cable:**

UL2725, (1P+2C)+A+B, OD: .189" [4.8mm] (28/24), Jacket Color: Black .

**Electrical Test:**

All Assemblies must be 100% Tested for Shorts, Open, Continuity, and Physical Appearance.

**Environmental:**

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED  
 ALL DIMENSIONS ARE INCHES [MM]  
 TOLERANCES: EXCEPT AS NOTED

.X ± .10	∅.X ± .10
.XX ± .020	∅.XX ± .015
.XXX ± .015	∅.XXX ± .010

**ADAM TECH**  
**INTERCONNECTS**

909 Rahway Avenue,  
 Union, NJ 07083  
 Phone: 908-687-5000  
 Fax: 908-687-5710

APPROVALS		DATE
DRAWN	HR	10/13/15
CHECKED	TW	10/13/15
APPROVED		

TITLE CUSTOMER ASSEMBLY, USB 2.0 PLUG TYPE A TO USB 2.0 SOCKET TYPE A		
SIZE X	PART NO. CA-USB-AM/AF-XFT	REV. A
REF: S00087T	SCALE: NTS	SHEET 1 OF 1

6

5

4

3

2

1