


# Product data sheet

Specifications

## Cable duct - 50 x 25 mm - without cover - grey



AK2GD2550

### Main

|                                    |  |
|------------------------------------|--|
| Product or component type          | Cable duct   |
| Accessory / separate part category | Cabling accessories  |
| Range compatibility                | Spacial (S3D)<br>Spacial (CRN)<br>Thalassa PLA<br>Thalassa PLS<br>Thalassa PLM |
| Device composition                 | Without cover  |
| Quantity per set                   | Set of 8   |

### Complementary

|                       |                              |
|-----------------------|------------------------------|
| Colour                | Grey (RAL 7030)              |
| Fixing mode           | By screws<br>Clip-on support |
| Material              | PVC (polyvinyl chloride)     |
| Height                | 50 mm                        |
| Length                | 2000 mm                      |
| Width                 | 25 mm                        |
| Net weight            | 0.46 kg                      |
| Total number of wires | 65                           |

### Environment

|                                       |                                      |
|---------------------------------------|--------------------------------------|
| Ambient air temperature for operation | -5...60 °C                           |
| Flame retardance                      | V-0 conforming to UL 94              |
| Fire resistance                       | 960 °C conforming to IEC 60695-2-1/1 |
| Standards                             | DIN 43659<br>VDE 0506<br>VDE 0660    |

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 10.0 cm |

|                              |          |
|------------------------------|----------|
| Package 1 Width              | 6.0 cm   |
| Package 1 Length             | 200.0 cm |
| Package 1 Weight             | 425.0 g  |
| Unit Type of Package 2       | PAL      |
| Number of Units in Package 2 | 560      |
| Package 2 Height             | 77.0 cm  |
| Package 2 Width              | 280.0 cm |
| Package 2 Length             | 120.0 cm |
| Package 2 Weight             | 263.0 kg |
| Unit Type of Package 3       | CAR      |
| Number of Units in Package 3 | 8        |
| Package 3 Height             | 6.0 cm   |
| Package 3 Width              | 10.0 cm  |
| Package 3 Length             | 200.0 cm |
| Package 3 Weight             | 3.4 kg   |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| RoHS exemption information | <a href="#">Yes</a>   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Recommended replacement(s)