

USB-C to USB-A Cable (M/M), USB 3.2 Gen 1 (5 Gbps), Thunderbolt 3 Compatible, 6 ft. (1.83 m)

MODEL NUMBER: **U428-006**



This USB-C to USB-A cable connects a USB Type-C (USB-C) device to the USB Type-A port on your tablet, computer or USB charger.

Features

Supports USB 3.1 Gen 1 This USB-C to USB-A cable features data transfer speeds up to 5 Gbps—10 times faster than USB 2.0 – and uses the same Type-A male connector as USB 3.0 devices.

USB Type-C (USB-C) Male Connector Unlike traditional USB cables that can be attached only one way, the fumble-free reversible USB-C plug ensures fast, easy connection every time.

Premium Design and Construction Gold-plated copper contacts, nickel-plated molded ends and a rugged PVC jacket provide for a lifetime of heavy use and superior conductivity. Foil shielding offers protection from EMI/RFI interference for reliable, error-free data communication.

Lifetime Limited Warranty The U428-006 is backed by a lifetime warranty, ensuring reliability and performance.

Highlights

- Connects a USB-C device to the USB-A port on your computer or charger
- 6-ft. (1.83 m) cable supports USB 3.1 Gen 1 data transfer speeds up to 5 Gbps
- Reversible USB-C male plug connects into a USB port in either direction
- Superior conductivity and data communication
- Backward compatible with previous USB generations
- Compatible with Thunderbolt™ 3 devices
- PD Charging Compliant

Applications

- Connect USB-C mobile devices and peripherals (such as portable hard drives) to your USB-A computer
- Charge and sync your USB-C mobile devices from a USB-A laptop or wall charger
- Ideal for those who need longer cables with USB-C to USB-A connections

System Requirements

- A device with a USB Type-C (USB-C) port
- A device with a USB Type-A port

Package Includes

- U428-006 USB 3.1 Gen 1 (5 Gbps) Cable, USB Type-C (USB-C) to USB Type-A M/M, 6-ft. (1.83 m)

Specifications

OVERVIEW	
UPC Code	037332218391
Technology	Thunderbolt; USB 3.x
Cable Type	Passive

PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.5MM
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Cable Length (cm)	182
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Relative Humidity	10% to 85% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB 3.0 A (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.1 Gen 1 (up to 5 Gbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.