


# Product data sheet

Specifications

## Cable duct - 75 x 50 mm - without cover - grey



AK2GD5075

### Main

Product or component type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial (S3D) Spacial (CRN) Thalassa PLA Thalassa PLS Thalassa PLM
Device composition	Without cover
Quantity per set	Set of 8

### Complementary

Colour	Grey RAL 7030)
Fixing mode	By screws Clip-on support
Material	PVC (polyvinyl chloride)
Height	2.95 in (75 mm)
Length	78.74 in (2000 mm)
Width	1.97 in (50 mm)
Net weight	1.94 lb(US) (0.88 kg)
Total number of wires	240

### Environment

Ambient air temperature for operation	23...140 °F (-5...60 °C)
Flame retardance	V-0 UL 94
Fire resistance	1760 °F (960 °C) IEC 60695-2-1/1
Standards	DIN 43659 VDE 0660 VDE 0506

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.97 in (5.0 cm)

Package 1 Width	2.95 in (7.5 cm)
Package 1 Length	78.74 in (200.0 cm)
Package 1 Weight	30.05 oz (852.0 g)
Unit Type of Package 2	PAL
Number of Units in Package 2	512
Package 2 Height	45.28 in (115.0 cm)
Package 2 Width	78.94 in (200.5 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	987.67 lb(US) (448.0 kg)
Unit Type of Package 3	CAR
Number of Units in Package 3	8
Package 3 Height	4.13 in (10.5 cm)
Package 3 Width	5.51 in (14.0 cm)
Package 3 Length	78.94 in (200.5 cm)
Package 3 Weight	15.43 lb(US) (7.0 kg)

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------

## Recommended replacement(s)