

## Specification Sheet

Part Number: 157-00405



Mount provides low insertion and high extraction forces which makes for a strong and easy installation.

Tie utilizes a strong hinge between the stud mount and strap head to provide superior holding ability.

Clamping rails increase grip on round bundles.

Thinner strap provides increased flexibility for improved ergonomics.

Wide Strap Cable Tie with .38" Stud Mount, 15.7" Long, 0.5" Wide, PA66HIRHSUV, Black, 300/bg

Article Number 157-00405

Type WSR380

Color Black (BK)

Quantity Per bag

**Product Description**  
The Wide Strap Stud Mount Cable Tie minimizes pinching on soft bundles and features a low profile head to provide compact bundling. A thinner strap provides increased flexibility for improved ergonomics. Available in various stud mount sizes, the wide strap tie utilizes a strong hinge between the stud mount and head to provide superior holding ability on a threaded stud.

**Short Description**  
Wide Strap Cable Tie with .38" Stud Mount, 15.7" Long, 0.5" Wide, PA66HIRHSUV, Black, 300/bg

Global Part Name WSR380-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial) 120.0

Minimum Tensile Strength (Metric) 535.0

Length L (Imperial) 15.7

Length L (Metric) 398.8

Fixation Method Weld Stud Fixing

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.5

Width W (Metric) 12.7

Bundle Diameter Min (Imperial) 0.38

Bundle Diameter Min (Metric) 9.5

Bundle Diameter Max (Imperial) 4.13

Bundle Diameter Max (Metric) 105.0

|                              |  |
|------------------------------|--|
| Stud Diameter (Metric)       | M10  |
| Stud Diameter (Imperial)     | 3/8  |
| Material                     | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| Material Shortcut            | PA66HIRHSUV  |
| Flammability                 | UL 94 HB   |
| UV Resistant (Yes/No)        | Yes  |
| Operating Temperature        | -40°F to +221°F (-40°C to +105°C)  |
| Reach Compliant (Article 33) | No   |
| ROHS Compliant               | Yes  |
| Package Quantity (Imperial)  | 300  |
| Package Quantity (Metric)    | 300  |
| Customs Number               | 3926909988   |

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar,

electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)