
**ROHS COMPLIANT** 

## PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	DCN 46496	6/17	GPF
Α	DCN 46873	9/17	STW
		·	



**MATERIAL**:

2X SMPM R/A FEMALE (3222-40002) **CONNECTORS:** 

CABLE: T-FLEX 405 (200-70-139)

SHRINK TUBING: M23053/5

PERFORMANCE:

50 OHMS IMPEDANCE:

FREQ. RANGE: DC TO 18.0 GHz. MATERIAL: **SEE NOTES** FINISH: SEE NOTES

SURFACE AREA: N/A

PROPRIETARY

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.

DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' ±15' RACTIC.

DECIMAL: X ±.0.
.XX ±.010
.XXX ±.005

INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994

THIRD ANGLE PROJECTION

## UNLESS OTHERWISE SPECIFIED

1) ALL DIMENSIONS ARE IN INCHES [MILLIMETERS]
2) ALL DIMENSIONS ARE AFTER PLATING,
3) BREAK CORNERS & EDGES 005 R. MAX.
4) CHAM. 1ST & LAST THREADS.
5) SURFACE ROUGHNESS 63-MIL-STD-10.
6) DIA: S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R.
7) REMOVE ALL BURRS

REDRAWN: JMS 10/02/17 RECHECKED: STW 10/02/17 REAPPROVED: STW 10/02/17

(12.000") 7032-7157 7032-7158 (24.000")

L(OAL)

(6.000")

SMPM FEMALE R/A TO SMPM FEMALE R/A FOR .085

CABLE ASSEMBLY

SV P/N

7032-7156

SIZE DWG. NO. 7032-7156-7158

SHEET 1 OF 1