


1	2
PIN	PIN
1 = BROWN 2 = WHITE 3 = BLUE 4 = BLACK 5 = GREY	1 = RED 2 = GREEN 3 = BLACK 4 = WHITE 5 = GREY



NOTE: PACKAGED 10 PER BAG

ROHS COMPLIANT

风

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
G. BROWN

DATE:
01/23/2019


UNITS IN INCHES [MM] DO NOT SCALE FROM DRAWING




CALE:	SHEET		OF		REV
NTS		1		2	3
NC NO	•				

FPM12A05IYYCR0Y

DESCRIPTION: M12 5 POSITION BRASS FEMALE PIGTAIL






NOTE: MATERIAL HOUSING: PBT UL94V-0, BLACK CONTACT: BRASS BRASS NUT: SHELL: BRASS □-RING: EPDM, BLACK FINISH CONTACT: GOLD PLATED, 104" Min. UNDER PLATE: NICKEL NUT: NICKEL PLATED NICKEL PLATED SHELL: ELECTRICAL RATED CURRENT: 4Α 60V RATED VOLTAGE: INSULATION RESISTANCE: 100MΩ MIN CONTACT RESISTANCE: $10m\Omega$ MAX WATER PROOF: IP67/68

OPERATION TEMPERATURE: -40°C ~ +85°C

RECOMMENDED PANEL CUT-OUT



ROHS COMPLIANT

M

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
G. BROWN

DATE:
01/23/2019

UNITS IN INCHES [MM] DO NOT SCALE FROM DRAWING

NorComp

CALE:	SHEET		OF		REV
NTS		2		2	3
WC NO					,

FPM12A05IYYCR0Y