



Product: 7406W ☑

MachFlex™, 11+1G C #20 Str BC, PVC Ins, TPE Jkt, PLTC

Request Sample

Product Description

MachFlex™ for High Flex, 11+1G Conductor 20AWG (19x32) Bare Copper, PVC Insulation, TPE Outer Jacket, PLTC

Technical Specifications

Physical Characteristics (Overall)

Conductor

Element	AWG	Stranding	Material	No. of Conductors
	20	19x32	BC - Bare Copper	11
Ground Wire	20	19x32	BC - Bare Copper	1
Conductor Co	ount:		12	2

Insulation

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.015 in

Color Chart

Number	Color		
1	Black and Numbered 1		
2	Black and Numbered 2		
3	Black and Numbered 3		
4	Black and Numbered 4		
5	Black and Numbered 5		
6	Black and Numbered 6		
7	Black and Numbered 7		
8	Black and Numbered 8		
9	Black and Numbered 9		
10	Black and Numbered 10		
11	Black and Numbered 11		
12	Green/Yellow		

Outer Shield



Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness
TPE - Thermoplastic Elastomer	0.363 in	0.042 in

Electrical Characteristics

Conductor DCR



Voltage



Temperature Range

UL Temp Rating:	90°C		
Operating Temperature Range:	-40°C (-5°C Flexing) To +90°C		
Other Temp Range:	Flexing: -5°C To +90 °C		

Mechanical Characteristics

Oil Resistance:	Yes
Flex Cycle Rating:	1 Million Flexes
Bulk Cable Weight:	82 lbs/1000ft
Max. Pull Tension:	156 lbs
Min. Bend Radius (Continuous Flexing):	3.6 in

Standards

NEC/(UL) Compliance:	PLTC
UL AWM Style Compliance:	AWM 20327
CSA AWM Compliance:	AWM I/II A/B

Applicable Environmental and Other Programs

Yes
Yes
Yes
Yes
EU Directive 2003/11/EC (BFR)
Yes

Suitability

Suitability - Non-Halogenated:	No
Suitability - Oil Resistance:	Yes - Oil Res II
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 UL Loading	
CSA Flammability:	FT4	
IEEE Flammability:	1202	
UL voltage rating:	300 V RMS	

Plenum/Non-Plenum

Plenum (Y/N):	No

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
7406W 060250	Chrome	Reel	250 ft	612825185550
7406W 0601000	Chrome	Reel	1,000 ft	612825185543
7406W 0605000	Chrome	Reel	5,000 ft	612825185567

Footnote: C - CRATE REEL PUT-UP.

History

Update and Revision:	Revision Number: 0.373 Revision Date: 05-05-2023

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.