
PROPRIETARY INFORMATION: PROPRIETARY OF GLOBTEK, INC., ANY REPRODUCTION, DI

PROPRIETARY OF GLOBTEK, INC. ANY REPRODUCTION, DISCLOSURE OR USE OF THIS DRAWING, IN WHOLE OR IN PART, IS HEREBY PROHIBITED EXCEPT AS SPECIFIED IN WRITING BY GLOBTEK,INC.

REVISION						
REV	DESCRIPTION	DATE	APPROVED			
A	INITIAL RELEASE, RFS.26790, DR	06/15/17	DR			
В	UPDATE BLACK WIRE CONNECTION FROM P4 -P4 TO P4-P2, RFS.27158	9/10/18	DR			

A	Wire color	$^{\circ}$
P1	Red	P1
P4	Black	P2

Important dimension "*"





Front view

Contents of this document

prior notice

are subject to change without

Foot Note:

1	Wire	NO-UL 22AWG*2C(RED BLACK) OD:3.5 Black
2	Connector	CONNECTOR TYPE A USB-A-04
3	Connector	M-BP70102-02554A0B CFE 2pin male magnetic connector
4	Ferrite core	/
5	Turns of ferrite core	/
6	SR Mold	PVC 60P BLACK
7	Core Mold	/
8	Connector Mold	PVC 60P BLACK

PART NO

DATE:

06/15/17

DASH

APRVD: DR

Note:

Mechanical:

Contact force: 70g±20g at 1.0 mm working stroke

Full stroke: 1.40 mm Life test: 50,000 cycles

Electrical:

Rated current & voltage: DC 12V, 2A Max. Contact resistance: 50 milliohm Max.

100% open & short test

DESCRIPTION

RELEASED

By N.Frost at 4:24 pm, Sep 10, 2018



Limitation of Use:

Globtek Inc. will not be liable for the safety and performance of these power product if unauthorized access and repair occurs. End user should consult the applicable UL,CSA or EN Standards for proper installation instruction.

Globtek product are not authorized for use as mission critical components in life support, hazardous environment, nuclear or aircraft applications without prior written approval from the CEO of Globtek Inc.

	TOLERANCES: DECIMALS ANGULAR		
		.xx +/- 0.1 .xxx +/005	+/- 1°
INIT.BY: DR	DATE: 06/15/17	MILLIMETERS .xx +/- 0.3 .xxx +/013	ANGULAR +/- 1°
DRAWN: NF	DATE: 06/15/17	FSCN No.: G, CC	SIZE A

REV.

SCALE: NONE

GlobTek, Inc.

TABULATION BLOCK

186 Veterans Dr. Northvale, NJ 07647 Tel. 201-784-1000 Fax 201.784.0111

DWG TITLE: MAGNETIC CABLE CONNECTOR

REV. B

PART NO: MAG2C2A11851MUSBA(R)

SHEET 1/1

NOTES