

## Specification Sheet

Part Number: 150-37791



Two-piece assembly allows mount to slide along strap, ensuring proper orientation.

Arrowhead-style mount provides low insertion and high extraction force.

Multiple material options provide solutions for any environment.

2-Piece Cable Tie/Arrowhead Mount, 6.5mm hole dia., 0.6-8.25mm Panel Thickness, PA66HIRHS, Black, 500/bg

Article Number 150-37791

Type T50ROSSFT6.5-16-3

Color Black (BK)

Quantity Per bag

Product Description HellermannTyton's Arrowhead Push Mount Tie Assembly is a two piece design allowing the mount to slide along the strap of the tie to ensure proper orientation. The arrowhead mount is designed for low insertion into a pre-drilled hole, while providing a high extraction force. The disc also protects against dirt and other impurities.

Short Description 2-Piece Cable Tie/Arrowhead Mount, 6.5mm hole dia., 0.6-8.25mm Panel Thickness, PA66HIRHS, Black, 500/bg

Global Part Name T50ROSSFT6.5-16-3-PA66HS/PA66HIRHS-BK

Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	7.87
Length L (Metric)	200
Fixation Method	Arrowhead
Identification Plate Position	none
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.181
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.197
Bundle Diameter Min (Metric)	5.0
Bundle Diameter Max (Imperial)	1.77
Bundle Diameter Max (Metric)	45.0
Height H (Imperial)	0.051
Height H (Metric)	1.3

Panel Thickness Min (Imperial)	0.098
Panel Thickness Max (Imperial)	0.138
Panel Thickness Min (Metric)	2.5
Panel Thickness Max (Metric)	3.5
Mounting Hole Diameter D (Imperial)	0.248 - 0.264
Mounting Hole Diameter D (Metric)	6.3 - 6.7 mm
Mounting Hole Diameter D Min (Imperial)	0.248
Mounting Hole Diameter D Max (Imperial)	0.26
Mounting Hole Diameter D Max (Metric)	6.7
Disc Diameter (Metric)	16.0
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HS PA66HIRHS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB

UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)