

## Specification Sheet

Part Number: 157-00017



Friction tab inside of fir tree allows tie to sit in mount without falling out prior to installation.

Initial fir tree serves as a locating feature for assistance in blind assembly applications.

Disc feature provides anti-rattle protection in high vibration applications.

1-Piece Cable Tie/Fir Tree Mount with Disc, 6.7"L, 0.27 - 0.28" Mounting Hole, PA66, Black, 100/pkg

Article Number 157-00017

Type OS170-FT7

Color Black (BK)

Quantity Per bag

Product Description Fir tree mounts, with cable ties, provide a secure grip in mounting holes and protect against dirt and other impurities. The mount provides low insertion and high extraction force, and slides along the cable tie for the proper orientation. This is sold as an assembly with the cable tie.

Short Description 1-Piece Cable Tie/Fir Tree Mount with Disc, 6.7"L, 0.27 - 0.28" Mounting Hole, PA66, Black, 100/pkg

Global Part Name OS170-FT7-PA66-BK

Minimum Tensile Strength (Imperial)	30.0
Minimum Tensile Strength (Metric)	147
Length L (Imperial)	6.7
Length L (Metric)	170.0
Fixation Method	Fir tree for round holes
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.21
Width W (Metric)	5.3
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.6
Bundle Diameter Max (Imperial)	1.18
Bundle Diameter Max (Metric)	30.0
Thickness T (Imperial)	0.055
Thickness T (Metric)	1.4

Panel Thickness Max (Imperial)	0.18
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	4.50
Mounting Hole Diameter D (Imperial)	0.27 - 0.28
Mounting Hole Diameter D (Metric)	6.8 - 7.2 mm
Mounting Hole Diameter D Max (Metric)	7.2
Disc Diameter (Metric)	16.0
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	No

ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)