


1. 旋转开关型号 ROTARY SWITCH MODEL MFR01-A1F06L1SA-R;
2. 额定值 RATING: 8A 125/250VAC(UL,C-UL)  
12A-8(3)A 250V~µT125/55(ENEC-17,CQC,CB)  
UL APPROVAL FILE NO.:E153399  
ENEC CERTIFICATE NO.:NO3691  
CQC CERTIFICATE NO.:10002049682  
CB CERTIFICATE NO.:NO56963/A1


3. 功能 FUNCTIONAL: 单极7个档位 SINGLE POLE 7 POSITIONS

4. 所有部件均使用环保材料

ALL MATERIALS USE IN CONFORMIY WITH THE RoHS DIRECTIVE



CIRCUIT DIAGRAM



PANEL CUTOUT

修正 REVISION	說明 DESCRIPTION	修订者 REVISED BY	SPECIFICATION				公差 TOLERANCES		TOLERANCES UNLESS OTHERWISE SPEC.±0.3/0.05,ANG.±2°			
△			製圖 DRAWN BY	設計 DESIGNED BY	校對 CHECKED BY	核准 APPROVED BY	單位 UNIT	mm	機種名稱 MODEL NAME	ROTARY SW	機種編號 MODEL NO.	MFR01-A1F06L1SA-R
△			王凡	刘美昌	刘美昌	刘美昌	比例 SCALE	2/1	六鈞電子五金有限公司 LEGION ELECTRONIC & HARDWARE CO., LTD.			
△			20-JUN-2016	20-JUN-2016	20-JUN-2016	20-JUN-2016	日期 DATE	2016.06.20				