



CIRCUIT DIAGRAM



PANEL CUTOUT

1. 额定值 RATING: 8A 125/250VAC (UL, C-UL)
12A-8(3)A 250V~ μ T125/55 (ENEC-17, CQC, CB)
2. 功能 FUNCTIONAL: 见电路图 SEE CIRCUIT DESCRIPTION
3. 接触电阻 CONTACT RESISTANCE: <50mΩ
4. 绝缘电阻 INSULATION RESISTANCE: >100MΩ (500VDC BETWEEN OPEN CONTACTS)
5. 耐电压 DIELECTRIC STRENGTH: >1500VAC 0.5mA 1 MINUTE
6. "○"表示关键尺寸 DENOTES CRITICAL DIMENSIONS

DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
RANGE	TOLERANCE				SCALE	NO			
5					LMC 2019.05.20	MAT'L	***	DRAWING NO.	REV.
4						MATERIAL NO.			
3	X	±0.30				MFR01-A1M03L1L-N		WIF119112	A
2	X.X	±0.20				LEGION ELECTRONIC & HARDWARE CO., LTD.			
1	X.XX	±0.10							
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'				