



1. 额定值 RATING: 8A 125/250VAC (UL, C-UL)
12A-8(3)A 250V~ μ T125/55 (ENEC-17, CQC, CB)
2. 功能 FUNCTIONAL: 见电路图 SEE CIRCUIT DESCRIPTION
3. 接触电阻 CONTACT RESISTANCE: <math>< 50\text{m}\Omega</math>
4. 绝缘电阻 INSULATION RESISTANCE:
>100MΩ (500VDC BETWEEN OPEN CONTACTS)
5. 耐电压 DIELECTRIC STRENGTH: >1500VAC 0.5mA 1 MINUTE
6. "○"表示关键尺寸 DENOTES CRITICAL DIMENSIONS



CIRCUIT DIAGRAM



PANEL CUTOUT

△5	→	△10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
△4	→	△9	→	RANGE	TOLERANCE				LMC	SCALE	NO		
△3	→	△8	→	X	±0.30				2019.05.20	MAT'L	***		
△2	→	△7	→	X.X	±0.20					MATERIAL NO.		DRAWING NO.	REV.
△1	→	△6	→	X.XX	±0.10							WIF119060	A
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'	LECION ELECTRONIC & HARDWARE CO., LTD.				MFR01-A1M06L4S-N			