




- NOTES-
1. MATERIAL SEE TABLE;
 2. ELECTRICAL PERFORMANCES:
 - 2-1. RATED CURRENT: 0.3A;
 - 2-2. CONTACT RESISTANCE: 90mΩ Max. with AC 20mV, 1kHz and 1mA;
 - 2-3. INSULATION RESISTANCE: 50mΩ min. With DC 100v;
 - 2-4. WITHSTANDING VOLTAGE: 100 VAC FOR 1 MINUTE MIN.
 3. MECHANICAL PERFORMANCES:
 - 3-1. DURABILITY: 30 CYCLES;
 - 3-2. OPERATION TEMPERATURE: -35°C To +85°C;
 - 3-3. NORMAL INSERT FORCE AT MATED POSITION: 5N MAX;



RECOMMENDED PCB LAYOUT
TOLERANCE: ±0.03

Ass'y High(H)	Plastic High	
	Male (H1)	Female (H2)
1.50	1.14	1.40
2.00	1.14	1.90
2.50	1.14	2.40
3.00	1.14	2.90
3.50	1.14	3.40
4.00	1.14	3.90

Ordering Information

HC-PBB40C - NDP - 0.4V - 02

No. of Pins: 10=120Pin, 10=10Pin, 12=12Pin, ...

Nature: DP=Male

PITCH: 0.4V=0.4mm

Pin	10	12	20	24	30	34	40	44	50	60	70	80	90	100	120
A	3.52	3.92	5.52	6.32	7.52	8.32	9.52	10.32	11.52	13.52	15.52	17.52	19.52	21.52	25.52
B	1.60	2.00	3.60	4.40	5.60	6.40	7.60	8.40	9.60	11.60	13.60	15.60	17.60	19.60	23.60
C	-	-	1.93	2.43	3.18	3.68	5.08	5.86	5.50	6.00	7.00	8.00	9.00	10.00	14.00
D	1.00	1.00	1.00	1.20	1.50	2.30	3.20	3.20	3.20	3.20	3.20	3.20	3.20	3.20	3.20

2	Housing	1	LCP	Glass:30%	Black
1	Terminal	N	C5191H	Ni 50~90u"UNDERPLATING, GOLD FLASH OVER ALL	
ITEM	Part Name	Q'TY	MATERIAL	MATERIAL	REMARK

			GENREL TOLERANCE	制 图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD				
			DIM	TOL	审 核 CHECK	产品名称 TITLE	0.4 双槽 立贴 公座 (BTB)	版 本 REV.	A
			X. X	±0.30	批 准 APPROVAL	产品料号 PART NO.	HC-PBB40C-NDP-0.4V-02	单 位 UNITS	mm
1	初版发行		X. XX	±0.20	比 例 SCALE	材 料 MATERIAL		页 次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X. XXX	±0.10	投 影 Projection				
			Angle	±3.0°					