



CIRCUIT DIRGRAM

NOTE:
 Rating: DC 12V 0.1A
 Operating Force: ≤36gf
 Lifetime: 50,000 Cycles

④	Contact Spring	—	1	Phosphor Bronze	Ag Clad	—
③	Terminal	—	2	Brass	Ag Plated	—
②	Base	—	1	NYLON	Black	—
①	Slider	—	1	NYLON	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE		 ELECTRONICS CO.,LTD		
DRAWN	LIUCAN	2023.8.25				
CHECKED				TITLE:	DETECTOR SWITCHS	
APPROVALS				PART NO.	K5-1654SA-01	
TOLERANCES ARE			30~以上 ±0.30	ANGLE	UNIT: mm	SCALE: 1:1
			10~30 ±0.20			
			5~10 ±0.15			
			~ 5 ±0.10			
				±2'	DRAWING NO.	SHEET 1 OF 1

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.