


Recommended PCB Layout



Specifications:

- 1.Rating: DC 30V 1.5A
- 2.Mating force: 3.75kgf Max
- 3.Unmating force: 1.02kgf Min
- 4.Lifetime:5000cycles

PART NO	外壳
U-A-24DD-W-22	铁壳
U-A-24DD-W-22T	铜壳

③	Base	—	1	NYLON	White
②	Terminal	—	4	Copper Alloy	Sn Plated
①	Housing	—	1	SPCC/Copper	Ni Plated
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING

APPROVALS		DATE		 ELECTRONICS CO.,LTD		
DRAWN	LIUCAN	2022.12.7				
CHECKED				TITLE: USB CONNECTOR		
APPROVALS				PART NO.		
TOLERANCES ARE		30~以上 ±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:
		10~30 ±0.25				
		5~10 ±0.20				
		~ 5 ±0.15				
		±2'	DRAWING NO.	SHEET 1 OF 1		

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
—	A	—	NEW	—	—	—