



SPECIFICATIONS  
 Current Rating:3.0AMP  
 Contact Resistance:10mΩMax  
 Dielectric Strength:Min 1000V RMS  
 Operation Temperature:-40°c to +105°c

Contact Material:Brass  
 Contact Clip(4/6 finger):Becu(C17200)  
 Accepted Pin:∅0.40 to 0.60mm  
 Insulator Material:Polyester(UL94V-0)  
 Standard: PPS  
 Soldering temperature: 260°C±5° 5S

### Ordering Information

XDM 254 C - \* - N - Z - \* - \*\*

Round Pin 圆针	No.of Rows 1=Single Row 2=Dual Row	No.of Pins 01-40 Pin	Type Z=直针 W=弯针 S=空指	Length 塑高	Contact Plating G0:Gold Flash G1:1u" Gold G2:3u" Gold G3:5u" Gold G4:10u" Gold G5:15u" Gold G6:30u" Gold S0:Gold Flash/Tin S1:Tin
-----------------	--	-------------------------	------------------------------	--------------	--

			GENERAL TOLERANCE	制图 DRAWING	深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd			
			DIM TOL	审核 CHECK				
			X.X ±0.30	批准 APPROVAL	产品名称 TITLE	2.54 单排 圆直排母 L7.43 (塑高3.0)	版本 REV.	A
			X.XX ±0.20	比例 SCALE	产品料号 PART NO.	XDM254C-1-N-Z-3.0-XX	单位 UNITS	mm
			X.XXX ±0.10		投影 Projection	材料 MATERIAL		页次 SHEET
1	初版发行		Angle ±3.0°					
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						