




**SCHEMATIC**



R:red	G:green
Y:yellow	B:black
W:white	T:transparent



PJ-3135-



Ø3.5 MATING PLUG

- SPECIFICATION**
- 1.Rating: DC 30V 0.5A
  - 2.Contact resistance: ≤30mΩ
  - 3.Insulation resistance: ≥100mΩ
  - 4.Withstand voltage: 500VAC
  - 5.Insertion and extraction force: 3-20N
  - 6.life test: 5,000 cycles

	MATERIAL	PLATING
terminal 2	Phosphor Bronze	tin
terminal 3	Phosphor Bronze	tin
terminal 4	Phosphor Bronze	tin
plastic	Pbt	

PJ-3136-

广东星坤科技股份有限公司

日期

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES



DSND	SCALE: N/A	MODEL TYPE: 3.5 PHONE JACK
DWN	VIEW:	PART NO.: PJ-313X-X
CHKD	UNIT: mm/in	DWG NO.:
APPD	SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED		WEIGHT
		SHEET
		REVISIC
		1/1
		A0