



孔位	A	B
2	0	5.4
4	4.2	9.6
6	8.4	13.8
8	12.6	18.0
10	16.8	22.2
12	21.0	26.4
14	25.2	30.6
16	29.4	34.8
18	33.6	39.0
20	37.8	43.2
22	42.0	47.4
24	46.2	51.6

使用温度范围 (Ambient temperature Range): $-25^{\circ}\sim+85^{\circ}$
 适用线规 (Applicable Wires): AWG 28#~20#
 适用基板厚度 (Applicable PCboard thickness): 1.7mm
 额定电压 (Voltage rating): 300V AC,DC
 额定电流 (Current rating): 4A
 接触电阻 (Contact Resistance): $<0.015\Omega$
 绝缘电阻 (Insulation Resistance): $\geq 1000M\Omega$
 耐压 (Withstand Voltage): 1000V/min
 材料 (Material)
 1. 基座: PA66 FV2
 2. 插针: 黄铜

—		new		2015/5/3	A	瀚源
ECN BO.		DESCRIPTION.		DATE.	REV.	
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1
Mikey	Tom	Jerry	PART NAME	9357WR-2xXXP	UNLESS OTHERWISE SPECIFIED, TOLERANCE:	X. ±0.25
			MODEL NAME	9357WR-2xXXP		X.x ±0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xx ±0.15
					ANGULAR	±3
					FILE.NO.	