






NOTES:
 Current Rating: 3.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 1000V AC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40°C to +125°C(Au)
 -40°C to +105°C(Sn)

Contact Material: Phosphor Bronze
 Contact plating: Au Or Sn over Ni
 Insulator Material: PA9T+33%G.F UL94V-0



Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Ordering Information

2134 - 1 XX M XX CUN X 1

No. of Pins per ROW: 02-40PIN

Contact Plating:
 G0=Gold Flash
 G3=10μ"Gold
 G4=15μ"Gold
 G5=30μ"Gold
 S0=Gold Flash/Matte Tin
 S3=10μ"Gold/Matte Tin
 S4=15μ"Gold/Matte Tin
 S5=30μ"Gold/Matte Tin
 SN=Tin
 SM=Matte Tin

Packing:
 T=Tube
 R=Tape&Reel

| Item | Pitch | Mating | DIM.B |
|-----------|-------|--------|-------|
| Standard | 2.54 | 1125B | 4.00 |
| Alternate | | | |

| Pin(Per Row) | 2-15P | 16-25P | 26-40P |
|--------------|-------|--------|--------|
| M | 0.10 | 0.15 | 0.20 |

| REV | DATE | MODIFICATION DESCRIPTION | CHANGE | DIM | TOL | APPROVE | DATE | PROJ. |
|-----|------------|-------------------------------|--------|-------------|---------|------------|-------|-------|
| A5 | 2023/05/22 | ADD VIEW | A5 | OPERATION | DRAW | DATE | SCALE | FIT |
| A4 | 2020/11/30 | Modify Flatness,Add VIEW&DIM. | A4 | X.X ±0.40 | XSR | 2023/05/22 | UNIT | mm |
| A3 | 2016/11/10 | Modify | A3 | X.XX ±0.25 | CHECK | DATE | SIZE | A4 |
| A0 | 2012/08/02 | NEW | ---- | X.XXX ±0.15 | APPROVE | DATE | SHEET | 1/1 |
| | | | | Angle ± 3° | | | PROJ. | |

PART NO.
2134-1XXMXXCUNX1

TITLE:
2.54mm FEMALE HEADER SINGLE ROW 180°SMT SIDE ENTER H=3.2

Customer NO.

WCON

Http: www.wcon.com

WCON-Dongguan
 Tel: +86 769 85358920
 Fax: +86 769 85358915
 E-mail: sales@wcon.com

WCON-Kunshan
 Tel: +86 512 57468408
 Fax: +86 512 57468468
 E-mail: salesks@wcon.com