




**D-SUBMINIATURE CONNECTORS:**  
**K88X Series**  
 Vertical PCB Mount High Profile

**K88X Series Dimensions**  
 Dimensions in mm




Number of Contacts (Shell Size)	Dimensions ( mm )				
	A	A1	B	C	D
9 (E)	16.33	16.92	24.99	30.81	19.18
15 (A)	24.66	25.25	33.32	39.14	27.51
25 (B)	38.38	38.96	47.04	53.04	41.00
37 (C)	54.84	55.42	63.50	69.32	57.71

A = Exterior of Female Shell (S)  
 A1 = Interior of Male Shell (P)

2D Drawing	IGES	STEP	3D PDF
Solder Profile	CofC RoHS Compliant	CofC REACH Compliant	UL Plastic File
Certificate of Origin	Check Stock	Request a Sample	Send Us An Email

Generated Part Number

Part Number Builder



**Series**

K88X - D-Subminiature Vertical Connector

**Contact Shell Size**

- E - 9 Contacts
- A - 15 Contacts
- B - 25 Contacts
- C - 37 Contacts

**Pin Type (L1)**

- D - 3.80mm

**Contact Type**

- P - Pin Contact (Plug)
- S - Socket Contact (Receptacle)

**Mounting Option**

- Blank - Through Hole
- BR - #4-40 Tin Plated 11.00mm Long Boardlocks
- BRJ - #4-40 Boardlocks and #4-40 Jackscrews
- K - #4-40 Bushings
- KJ - #4-40 Bushings and #4-40 Jackscrews

Contact Kycon for plating and Other Options