

Product Features

P1dB's P1AD-24F29F is a straight 2.4mm Female to 2.92mm Female adapter that operates to 40 GHz with a maximum VSWR of 1.25:1. It has a Stainless Steel body and meets operating temperatures from -85 to 125 degrees Celcius.

P1dB offers a large selection of standard and precision 50 Ohm RF adapters for lab, aerospace, industrial and commercial applications. In-series and between series options include 1.85mm, 2.4mm, 2.92mm, 3.5mm, SMA, Type N, TNC and BNC.



Electrical Specification: T_{Ambient} = 25° C

Parameter	Frequency Range	Units	Min	Typical	Max	Notes
Impedance				50.0		

Mechanical And Environmental Specifications:

Parameter	Description	Notes
Connector 1	2.4mm Female	
Connector 2	2.92mm Female	
Orientation	Straight	
Mount Type	None	
RoHS Compliance	Yes	

Product Notes