





- MATERIAL:

- 1. Insulator: PBT+30%Glass Fiber
- 2. Contact: Brass
- 3. Contact Plated: Gold Flash over Tin Or Glod Plated Or Tin Plated
- 4. Shell: Steel, Nickel Plated

= SPECIFICATION:

- 1. Current Rating: 3 AMPS
- 2. Insulation Resistance: 100M Ω MIN. At 500VDC
- 3. Dielectric Strength: 500V for One minute
- 4. Operation Temperature: -55 $^{\circ}$ C~+105 $^{\circ}$ C.

*【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】



RECOMMEND PCB LAYOUT (T=1.6)
PCB TOLERANCE: ±0.05

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: DR25M双锁	
		PAR	D-SUB-DR-25PCG-BB
DECIMALS:	ANGLES:	DWN	
X.X±0.30	X.*±5'	CHKD	
X.XX±0.25	X.X'±2'	APVD	
X.XXX±0.15	X.XX'±1'	SCALE N:A	UNIT:MM
		SIZE:A4	SHEET:1F1
CUSTOMER COPY			REV:A