





REV.	ECN NO.	REVISED	DATE



工程部
2017-07-06
LQ. HUANG

- 技术要求:
- 1、毛刺高度≤0.03mm;
 - 2、部件要求平整,无变形、裂纹、损伤等外观缺陷;
 - 3、未注圆角:R0.2;
 - 4、带△尺寸为重点管控尺寸.

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com	
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND YangFeng	DATE 2017-07-06
		CHKD ZhouRuicai	DATE 2017-07-06
		APVD XueShunyong	DATE 2017-07-06
WEIGHT: 9		SCALE: 4:1	SIZE: A4
SHEET 1 OF 1		VIEW:	
		UNIT: mm	REV.: A/0
		OBJECT: MY	
		TITLE: BS-2032-11 Au 正极端子	
		PART NO.: MY-2032-11ZJDZ	
		DRAW NO.:MY-CP-0378	

1	TERMINAL(+)	1	PHOSPHOR BRONZE, T=0.20mm	Au-Plating
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR