





修 订 REV NO	标 记 MARK	修 改 描 要 REVISION DESCRIPTION	签 名 SIGNATURE	日 期 DATE
		NEW DRG		2016-03-12



Dimensions list

Contacts Per row	Dimensions		Contacts Per row	Dimensions	
	A	B		A	B
2*1	2.0	0	21	42.0	40.0
2	4.0	2.0	22	44.0	42.0
3	6.0	4.0	23	46.0	44.0
4	8.0	6.0	24	48.0	46.0
5	10.0	8.0	25	50.0	48.0
6	12.0	10.0	26	52.0	50.0
7	14.0	12.0	27	54.0	52.0
8	16.0	14.0	28	56.0	54.0
9	18.0	16.0	29	58.0	56.0
10	20.0	18.0	30	60.0	58.0
11	22.0	20.0	31	62.0	60.0
12	24.0	22.0	32	64.0	62.0
13	26.0	24.0	33	66.0	64.0
14	28.0	26.0	34	68.0	66.0
15	30.0	28.0	35	70.0	68.0
16	32.0	30.0	36	72.0	70.0
17	34.0	32.0	37	74.0	72.0
18	36.0	34.0	38	76.0	74.0
19	38.0	36.0	39	78.0	76.0
20	40.0	38.0	40	80.0	78.0

SPECIFICATIONS
 Current Rating: 3Amps
 Insulator resistance: 5000 Megchms min.
 Dielectric Withstanding: AC 500v
 Operating Temperature: \sim 40° +105° C
 Contact Material: Brass
 Insulator Material: pa6t
 Plating: Glod flash
 铜针: 65铜
 电镀: Gold flash
 UNSPECIFIED TOLERANCE: \pm 0.20

深圳市华德共创科技有限公司
 Shenzhen Huade co-create Technology Co.,LTD
 电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表			TITLE: 产品名称: 2.0直插排针L8.7/2.8/3.9					
X.X	\pm 0.30	X.X*	\pm 3°	APPD: 核准:	PART NO: 产品编号: HDGCPH20-PZ2-XX			
X.XX	\pm 0.20	X.XX*	\pm 2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT	CODE NUMBER
X.XXX	\pm 0.10	X.XXX*	\pm 1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm	A001