

HSF

NOTES:


Current Rating: 2.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 500V AC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40℃ to +105℃

Contact Material: Phosphor Bronze
 Contact plating: Au Or Sn over Ni
 Insulator Material: PA9T+33%G.F UL94V-0

Ordering Information

2240 - 2 XX M XX CUN X X X

No. of Pins per ROW: 02~40Pin
 Contact Plating:
 C0=Gold Flash
 G3=10μr Gold
 G4=15μr Gold
 G5=30μr Gold
 SP=Gold Flash/Tin
 S3=10μr Gold/Tin
 S4=15μr Gold/Tin
 S5=30μr Gold/Tin
 SN=Tin
 SM=Matte Tin
 Packing:
 T=Tube
 P=Tube+CAP
 R=Tube&Reel+CAP
 Series No.
 I=Type 1
 2=Type 2



Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)

Item	Pitch	Mating
Standard	2.00	1215/1220
Alternate		

A2	2023/02/14	Modify Flatness	OPERATION	DRAW	DATE	SCALE	PART NO.	TITLE: 2.0mm Female Header DUAL ROW 180SMT H=4.0 W=4.5 Customer NO.
A1	2022/06/22	Modify P/N,Add 2*2P-2*3P CAP	X.X	XSR	2023/02/14	mm	SEE TABLE	
A0	2012/07/12	NEW	X.XXX	CHECK	DATE	A4		
REV	DATE	MODIFICATION DESCRIPTION	ANGLE	APPROVE	DATE	1/1		
			DIM	TOL	PROJ.			

Pin(Per Row)	M	0.10	0.15	0.18
2-15P	16-25P	26-40P		

TITLE	PART NO.	A1
TYPE 1	2240-2XXMXXCUNX1	
TYPE 2	2240-2XXMXXCUNX2	

WCON

Http: www.wcon.com

WCON-Dongguan Tel: +86 769 85358920
 WCON-Kunshan Tel: +86 512 57468408
 Fax: +86 769 85358915
 Fax: +86 512 57468468
 E-mail: sales@wcon.com E-mail: sales@wcon.com