







P.C.B LAYOUT TOP VIEW



SCHEMATIC



8					TOLERANCE									
7					UNLESS SPECIFIED									
6					UP TO 5mm: ±0.1	ANGULAR	A1	2018.12.24	標原尺寸13.4更新為12.5, 新增尺寸1.45, 取消原尺寸11.0					
5	彈片腳	PBS	1	Ag-PLATED	ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS			BY	APPD	
4	插片腳	BRASS	1	Ag-PLATED	TITLE: DC JACK			UNIT : MM	ROHS	DWN				
3	平片	BRASS	1	Ag-PLATED	MODEL: DC-044G-2.0-PU-G			SCALE: 1:1	COMPLIANT	CHK'D				
2	圓針	BRASS	1	Ag-PLATED	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司							APPD		
1	基座	PA9T	1									PRO.AGL:		
NO.	PART	NAME	MATERIAL	QTY	FINISHING									